

Acrylic Extruded Satin Tube Specifications

Outer Dia. (mm)	Inner Dia. (mm)	Thickness (mm)	Outer Dia. Tolerance	Length (mm)
5	3	1	± 0.15	2000
6	4	1	± 0.15	2000
7	5	1	± 0.15	2000
8	6	1	± 0.15	2000
8	5	1.5	± 0.15	2000
10	8	1	± 0.20	2000
10	7	1.5	± 0.20	2000
10	6	2	± 0.20	2000
12	10	1	± 0.20	2000
12	8	2	± 0.20	2000
12	6	3	± 0.20	2000
13	9	2	± 0.20	2000
13	7	3	± 0.20	2000
14	10	2	± 0.20	2000
14	8	3	± 0.20	2000
15	13	1	± 0.20	2000
15	11	2	± 0.20	2000
15	9	3	± 0.20	2000
16	12	2	± 0.30	2000
16	10	3	± 0.30	2000
18	14	2	± 0.30	2000
18	12	3	± 0.30	2000

Acrylic Extruded Satin Tube Specifications

Outer Dia. (mm)	Inner Dia. (mm)	Thickness (mm)	Outer Dia. Tolerance	Length (mm)
20	18	1	± 0.30	2000
20	16	2	± 0.30	2000
20	14	3	± 0.30	2000
22	18	2	± 0.30	2000
22	16	3	± 0.30	2000
25	21	2	± 0.40	2000
25	19	3	± 0.40	2000
28	24	2	± 0.40	2000
28	22	3	± 0.40	2000
30	26	2	± 0.40	2000
30	24	3	± 0.40	2000
30	22	4	± 0.40	2000
30	20	5	± 0.40	2000
32	28	2	± 0.40	2000
32	26	3	± 0.40	2000
32	24	4	± 0.40	2000
35	31	2	± 0.40	2000
35	29	3	± 0.40	2000
38	34	2	± 0.40	2000
38	32	3	± 0.40	2000
38	30	4	± 0.40	2000
38	28	5	± 0.40	2000
40	36	2	± 0.40	2000

Acrylic Extruded Satin Tube Specifications

Outer Dia. (mm)	Inner Dia. (mm)	Thickness (mm)	Outer Dia. Tolerance	Length (mm)
40	34	3	± 0.40	2000
40	32	4	± 0.40	2000
40	30	5	± 0.40	2000
45	41	2	± 0.40	2000
45	39	3	± 0.40	2000
45	37	4	± 0.40	2000
45	35	5	± 0.40	2000
50	46	2	± 0.40	2000
50	44	3	± 0.40	2000
50	42	4	± 0.40	2000
50	40	5	± 0.40	2000
60	56	2	± 0.40	2000
60	54	3	± 0.40	2000
60	52	4	± 0.40	2000
60	50	5	± 0.40	2000
70	66	2	± 0.60	2000
70	64	3	± 0.60	2000
70	62	4	± 0.60	2000
70	60	5	± 0.60	2000
80	76	2	± 0.60	2000
80	74	3	± 0.60	2000
80	72	4	± 0.60	2000
80	70	5	± 0.60	2000

Acrylic Extruded Satin Tube Specifications

Outer Dia. (mm)	Inner Dia. (mm)	Thickness (mm)	Outer Dia. Tolerance	Length (mm)
90	86	2	± 0.60	2000
90	84	3	± 0.60	2000
90	82	4	± 0.60	2000
90	80	5	± 0.60	2000
100	96	2	± 0.80	2000
100	94	3	± 0.80	2000
100	92	4	± 0.80	2000
100	90	5	± 0.80	2000
110	104	3	± 1.00	2000
110	102	4	± 1.00	2000
110	100	5	± 1.00	2000
120	114	3	± 1.00	2000
120	112	4	± 1.00	2000
120	110	5	± 1.00	2000
125	119	3	± 1.00	2000
125	117	4	± 1.00	2000
125	115	5	± 1.00	2000
130	124	3	± 1.20	2000
130	122	4	± 1.20	2000
130	120	5	± 1.20	2000
133	127	3	± 1.20	2000
133	125	4	± 1.20	2000
133	123	5	± 1.20	2000

Acrylic Extruded Satin Tube Specifications

Outer Dia. (mm)	Inner Dia. (mm)	Thickness (mm)	Outer Dia. Tolerance	Length (mm)
140	134	3	± 1.20	2000
140	132	4	± 1.20	2000
140	130	5	± 1.20	2000
150	144	3	± 1.20	2000
150	142	4	± 1.20	2000
150	140	5	± 1.20	2000
160	154	3	± 1.50	2000
160	152	4	± 1.50	2000
160	150	5	± 1.50	2000
170	164	3	± 1.50	2000
170	162	4	± 1.50	2000
170	160	5	± 1.50	2000
180	174	3	± 1.80	2000
180	172	4	± 1.80	2000
180	170	5	± 1.80	2000
185	179	3	± 1.85	2000
185	177	4	± 1.85	2000
185	175	5	± 1.85	2000
200	194	3	± 2.00	2000
200	192	4	± 2.00	2000
200	190	5	± 2.00	2000
230	222	4	± 2.30	2000
230	220	5	± 2.30	2000

<https://www.smeacrylic.com.tw/>

Acrylic Extruded Satin Tube Specifications

Outer Dia. (mm)	Inner Dia. (mm)	Thickness (mm)	Outer Dia. Tolerance	Length (mm)
250	242	4	± 2.50	2000
250	240	5	± 2.50	2000

Acrylic Extruded Satin Tube Features

- Satin Tube has a warm and soft surface.
- Satin Tube is also insensitive to traces of wear and finger marks.

Acrylic Extruded Satin Tube Application

- Installation of artwork
- Lampshade

Acrylic Extruded Satin Tube Attention

- Do not coexist with other organic solvents, let alone expose them to organic solvents.
- Cannot be used at temperatures above 85 degrees Celsius.

Acrylic Extruded Satin Tube Specifications – Customized

- The above are the specifications of Acrylic Extruded Satin Tube Specifications. Customize colors and sizes, please contact us.

<https://www.smeacrylic.com.tw/>

S·M·E ACRYLIC Products

Acrylic Tube Extruded Acrylic Rod Acrylic Sheets, Acrylic Blocks

Acrylic Accessories Acrylic Light Guide Acrylic Bars, Acrylic Profiles

Acrylic Diffusers, LGP, Reflector Acrylic Curtain Wands Diamond Edge

Polishing Machine